



Dear Valued Customer.

ULVAC Components News

End of support and maintenance related to vacuum pumps

Thank you for the continuous business with us.

Regarding our vacuum pumps, we would like to summarize and report the models that have already been supported and the models that will be discontinued after 7 years have passed since the production was stopped. We will continue to provide maintenance services as much as possible for models that have been discontinued and are still being supported.

It is expected that some parts will become difficult to supply due to discontinuation of production by manufacturers and legal regulations. In addition, we recommend updating to the current model in order to prevent troubles due to unrepairable.

We appreciate and value our business relationship and look forward to your continued interest in our products.

- Details -

1. Object product

Please refer to the attached file

"PN-WP01-007-00_List of vacuum pump models which support has ended"

2. Support termination date

Please refer to the attached file

"PN-WP01-007-00_List of vacuum pump models which support has ended"

3. Period for maintenance service

Please refer to the attached file

"PN-WP01-007-00_List of vacuum pump models which support has ended"

Sincerely

Toshio Tanabe
Senior Manager
Components Business Planning Dept.

End of Document

List of vacuum pump models which support has end

■ Models for which support will soon end

Type	Model	Scheduled end of support date
Mechanical booster pump	PMB series PMB-003C(M)	2022,December,30,
Dry vacuum pump	CR-A series CR16A CR30A CR60A CR300A	2024,January,31.
Sputter ion pump	GST series GST-07L	2024,July,31.
Turbo molecular pump	UTM series UTM-50 UTM-150 UTM-300 UTM-500 UTM-1500	2026,April,30.
Turbo molecular pumping system	YTP series YTP-50M/SA YTP-150M/SA YTP-300M/SA YTP-500M/SA	2026,April,30.
Oil diffusion pump	ULK series ULK-14A for 3,15kW heater	2029,June,30.

■ Models for which support has already ended

Type	Model		
Dry vacuum pump	ER series ER80 ER150 ER400 ER600 ER1200		
	PDR series PDR-060CL(H) PDR-090A,AD PDR-090B PDR-090CL(H) PDR-180C		
	PVD series	PVD-150 PVD-180K PVD-300	
		XD series XD-300 XD-600 XD-900	
		PCD PCD-060A	
	Oil rotary vacuum pump	D- (D) series D-330 (D) D-650 (D) D-650D LTS D-950 (D) D-950D LTS D-950CP D-240D D-240DK	
		D- (D)K series D-330 (D)K D-650 (D)K D-950 (D)K	
		EC series	EC402 EC403 EC602 EC603 EC801 EC803
			PKS series PKS-008 PKS-030 (II type) PKS-060
			Mechanical booster pump

Type	Model	
Turbo molecular pump	UTM series UTM-3000 UTM-300FW UTM-700FW UTM-1200FW UTM-2000FW UTM-3300FW	
	UTM-FW series	
	UTM-FH series UTM-3303FH	
	UTM-M series UTM-300M UTM-500M UTM-1500M	
	for UTM series T1~8	
	for UTM-FW/FH series D1 D2	
	Oil diffusion pump	PFL series PFL-02 PFL-04 PFL-06 PFL-08 PFL-10 PFL-14
		F series F-250 F-600 F-1200
U series U-250 U-600 U-1200		
PEL series PEL-06 PEL-14		
Mercury diffusion pump		PFH series PFH-02 PFH-04 PFH-05 PFH-06 PFH-08
		Controller for Sputter ion pump GST series GST-03L
		Oil diffusion ejector pump B-50K B-50K

List of vacuum pump models which support has ended

PN-WP01-007-00
2022.August.12.

■ Models for which support will soon end

(2/3)

Type	Model		Scheduled end of support date
Vacuum angle valve	VLH series	VLH-U1	2023.June.30.
		VLH-US-50KF	
Vacuum angle valve	VLP series	VLP-U1	2023.June.30.
		VLP-US-50KF	
High vacuum gate valve	VTP series	VTP-U3A	2023.June.30.
		VTP-U8SR	
Ultra-high vacuum valve	VULP series	VULP-100CM	2023.June.30.
		VULP-65F	
Ultra-high vacuum valve	VULH series	VULH-100CM	2023.June.30.
		VULH-65F	
Ultra-high vacuum valve	VULPA-L series	VULPA-L-25KF	2023.June.30.
		VULPA-L-50KF	
High vacuum gate valve	VGEB series	VGEB-065	2023.June.30.
Poppet	Poppet	1P	2023.June.30.
		4P	
Oil filtration system	OF series	OF-2	2023.October.1.
		OF-3	
Variable orifice valve	VOP series	VOP-8	2028.March.31.
		VOP-20	
Atmosphere-Vacuum direct gate valve	IAD series	IAD-45-450	2028.March.31.
		IAD-250-1240	
Manual high vacuum gate valve	VAH series	VAH-U100	2028.March.31.
		VAH-U150	
Pneumatic high vacuum valve	VAP series	VAP-U100	2028.March.31.
		VAP-U150	
Gate valve	VIAD series	VIAD-50-330	2028.March.31.
		VIAD-60-200	
		VIAD-60-350	
Gate valve	VIAC series	VIAC-45-280	2028.March.31.
		VIAC-120-500	
Cold trap	CT series	CT-25	2029.September.30.
Oil trap	OT series	CT-100	
		OT-50	
		OT-80	
Powder adsorption trap	TRO series	OT-100	
		TRO-50	
		TRO-80	
Water cooling trap	WT series	TRO-100	
		WT-25	
		WT-50	
		WT-80	
Vacuum rubber hose	R series	WT-100	Until the end of stock
		R-5	
		R-50	

List of vacuum pump models which support has ended

PN-WP01-007-00
2022.August.12.

■ Models for which support will soon end

(3/3)

Type	Model		Scheduled end of support date
Foreline trap	UFT series		Until the end of stock
Ultra-high vacuum flange	UFC series		
Aluminum gasket for UFC flange	UFE series		
Fitting	IFS, IFE, IFT, IFX, IFB, CFH, series		
Rotary motion feedthrough	TDU series		
Straight motion feedthrough	TSU series		
Current motion feedthrough	CMS series		
Ultra-high vacuum zero length view port	TVU series		
Ultra-high vacuum valve	VUH series		
Air inlet valve	10AIV series		
Variable leak valve	VLV-3D		
Sorption pump	PSM series	PSM-10B	
Titanium getter pump	PGT/GGT series		
Alfoil roll	Alfoil roll	0.08t x 710W x 100M	Until the end of stock
		0.08t x 400W x 100M	
Synthetic oil for vacuum pump	ULVOIL series	R-7000	Until the end of stock
Vacuum pump oil	ULVOIL series	R-7	Until the end of stock
		R-4	
Base with handle casters for PVD			Until the end of stock

■ Models for which support has already ended

Type	Model	
Manual high vacuum gate valve	VAH series	Over 8B
Double acting high vacuum gate valve	VAP series	Over 8B
Ultra-high vacuum valve	VUH series	VUH-651C
Ultra-high vacuum gate valve	VUGP series	All models
	VUGH series	All models
High vacuum exhaust system	YM series	YM-100B
		YM-300
		YM-600A
	YMW series	YMW-100
		YMW-600
	YH series	YH-350A
		YH-500A
YM-VD series		
YM-VS series		
Pumping system	YDP series	YDP-04
		YDP-10
Cold trap	LCT series	LCT-04
		LCT-06
Oil mist trap	TMX series	TMX-40
		TMX-60
		TMX-80
	TM series	TM-80
ULVOIL	ULVOIL	R-7500
		R-8000
Clean foil		20μm
		50μm