

油拡散エゼクターポンプ_PBLシリーズ 代替ポンプ油_性能比較表

到達圧力 (Ultimate pressure) Pa		
機種 (Model)	ULV0IL_B-6	ULV0IL_B-50K
PBL-02	2.7×10^{-2}	2.7×10^{-2}
PBL-04		
PBL-06		
PBL-10		
PBL-14		
PBL-20		

排気速度 (Pumping speed) L/s		
機種 (Model)	ULV0IL_B-6	ULV0IL_B-50K
PBL-02	80	80
PBL-04	200	300
PBL-06	500	600
PBL-10	1,800	1,800
PBL-14	4,000	4,000
PBL-20	7,000	8,000

臨界背圧 (Maximum allowable fore pressure) Pa		
機種 (Model)	ULV0IL_B-6	ULV0IL_B-50K
PBL-02	40	27
PBL-04		40
PBL-06		80
PBL-10		40
PBL-14		90
PBL-20		40