



Dear customers,

ULVAC Components News

End of support and maintenance

Thank you for the continuous business with us.

Regarding our vacuum pumps, we would like to summarize and report the models that have already been supported and the models that will be discontinued after 7 years have passed since the production was stopped. We will continue to provide maintenance services as much as possible for models that have been discontinued and are still being supported. It is expected that some parts will become difficult to supply due to discontinuation of production by manufacturers and legal regulations. In addition, we recommend updating to the current model in order to prevent troubles due to unrepairable. We appreciate and value our business relationship and looks forward to your continued interest in our products.

- Details -

■ Models for which support will soon end

Type	Model		Scheduled end of support date
Sorption pump	PSM	PSM-10B	28-Feb-2027
Titanium getter pump	PGT/GGT		
Oil diffusion pump	ULK	3.15kW heater for ULK-14A	
Cold trap	CT	CT-25	30-Sep-2029
		CT-40	
		CT-50	
		CT-80	
		CT-100	
Oil trap	OT	OT-50	
		OT-80	
		OT-100	
Powder adsorption trap	TRO	TRO-50	
		TRO-80	
		TRO-100	
Water cooling trap	WT	WT-25	
		WT-50	
		WT-80	
		WT-100	
Turbo molecular pump	UTM-FW	UTM-350FW	28-Dec-2029
		UTM-480FW	
		UTM-800FW	
		UTM-1001FW	
		UTM-1400FW	
		UTM-2300FW	
		UTM-3301FW	
	UTM-FH	UTM-350FH	
		UTM-480FH	
		UTM-800FH	
		UTM-1001FH	
		UTM-3303FH	
		UTM-6300FH	
Power supply for turbo molecular pump	for UTM-FW/FH	D3	
Oil rotary vacuum pump	VD	VD151	30-Jun-2030
		VD201	
Oil diffusion ejector pump	PBL	PBL-02	31-Dec-2033
		PBL-04	
		PBL-06	
		PBL-10	
		PBL-14	

Next



■ Models for which support has already ended

Type	Model		Type	Model	
Dry vacuum pump	ER	ER80	Turbo molecular pump	UTM	UTM-3000
		ER150			UTM-300FW
		ER400			UTM-700FW
		ER600			UTM-1200FW
		ER1200			UTM-2000FW
	PDR	PDR-060CL(H)			UTM-3300FW
		PDR-090A,AD		UTM-FH	UTM-3302FH
		PDR-090B		UTM-M	UTM-300M
		PDR-090CL(H)			UTM-500M
		PDR-180C			UTM-1500M
	CR-A	CR16A		UTM	UTM-50
		CR30A			UTM-150
		CR60A			UTM-300
		CR300A			UTM-500
					UTM-1500
Oil rotary vacuum pump	PVD	PVD-150	Power supply for turbo molecular pump	for UTM	T1~8
		PVD-180K		for UTM-FW/FH	T1~8
		PVD-300			D1
					D2
	XD	XD-300	Turbo molecular pumping system	YTP	YTP-50M/SA ※YTP-50MB/SAB is excluded.
		XD-600			YTP-150M/SA
		XD-900			YTP-300M/SA ※YTP-300MB/SAB is excluded.
	PCD	PCD-060A			YTP-500M/SA
			Oil diffusion pump	PFL	PFL-02
	D- (D)	D-330 (D)			PFL-04
		D-650 (D)			PFL-06
		D-650D LTS			PFL-08
		D-950 (D)			PFL-10
		D-950D LTS			PFL-14
		D-950CP		F	F-250
		D-240D			F-600
		D-240DK			F-1200
	D- (D)K	D-330 (D)K		U	U-250
		D-650 (D)K			U-600
		D-950 (D)K			U-1200
	EC	EC402		PEL	PEL-06
		EC403			PEL-14
		EC602	Mercury diffusion pump	PFH	PFH-02
		EC603			PFH-04
		EC801			PFH-05
		EC803			PFH-06
	PKS	PKS-008			PFH-08
		PKS-030 (Ⅱ type)	Controller for sputter ion pump	GST	GST-03L
		PKS-060			GST-07L ※GST-07L-B is excluded.
		PKS-070 ※PKS-070B is excluded.	High vacuum pumping system	YM	YM-100B
Mechanical booster pump	PMB	PMB-001A			YM-300
		PMB-001B(F)			YM-600A
		PMB-001C(M)		YMW	YMW-100
		PMB-003			YMW-600
		PMB-003C(M)		YH	YH-350A
		PMB-006			YH-500A
		PMB-006A(S)		YM-VD	
		PMB-006B			
		PMB-006C(M)	Pumping system	YDP	YDP-04
		PMB-010			YDP-10
		PMB-010A	Cold trap	LCT	LCT-04
		PMB-010B			LCT-06
		PMB-012C(M)	Oil mist trap	TMX	TMX-40
		PMB-020			TMX-60
		PMB-020A			TMX-80
		PMB-020B			
		PMB-024C(M)		TM	TM-80
		PMB-035			
		PMB-035A			
		PMB-055			
		PMB-055A			
		PMB-040B			
		PMB-060B			

Sincerely

Munenori Tada
Sales Department Senior Manager
Components Business Unit

End of Document