



Dear customers,

09 June 2023

ULVAC Components News

Sales Termination

Please be informed that we will stop sales of the following product considering the ordered quantity in recent years.

We appreciate your continuous supports.

- Details -

1. Object products

Related parts of discontinued models of vacuum gauge (see attached file)

2. Sale end date

31 July 2023

*The above schedule may be changed depending on the stock status.

3. Attached file

Discontinued item list <PN-VG01-025-00E>

Sincerely

Toshio Tanabe
Senior Manager
Sales Dept.
Components Division

End of Document

Duscontinued item list

PN-VG01-025-00E

R 3 code	Model	Discription
	Pirani vacuum gauge (old model)	【Option&Parts】
210004447600	Sensor cable 4M	For GP-1000/GP-2000
210004447700	Sensor cable 10M	For GP-1000/GP-2000
210004443100	Sensor cable 15M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004443200	Sensor cable 20M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004443300	Sensor cable 25M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004443400	Sensor cable 30M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004443500	Sensor cable 35M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004443600	Sensor cable 40M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004443700	Sensor cable 50M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004489300	Sensor cable 60M	For GP-1S(RY)/GP-2A(RY), WP socket type
210004443800	Sensor cable 100M	For GP-1S(RY)/GP-2A(RY), WP socket type
210005118300	Sensor cable 4M 10pcs/set	For GP-1S(RY)/GP-2A(RY), WP socket type
210005118400	Sensor cable 10M 10pcs/set	For GP-1S(RY)/GP-2A(RY), WP socket type
210004402800	Sensor cable 2M	For Box unit BPR-WP
210004402900	Sensor cable 5M	For Box unit BPR-WP
210004403000	Sensor cable 10M	For Box unit BPR-WP
210004403100	Sensor cable 15M	For Box unit BPR-WP
210004403200	Sensor cable 20M	For Box unit BPR-WP
210004715000	Sensor cable 25M	For Box unit BPR-WP
210004403300	Sensor cable 30M	For Box unit BPR-WP
210004715100	Sensor cable 35M	For Box unit BPR-WP
210004715200	Sensor cable 40M	For Box unit BPR-WP
210004715300	Sensor cable 45M	For Box unit BPR-WP
210004403400	Sensor cable 50M	For Box unit BPR-WP
210004715400	Sensor cable 55M	For Box unit BPR-WP
210004715500	Sensor cable 60M	For Box unit BPR-WP
210004403500	Sensor cable 100M	For Box unit BPR-WP
210004403600	Sensor cable 2M	For Box unit BPR-WPB
210004403700	Sensor cable 5M	For Box unit BPR-WPB
210004403800	Sensor cable 10M	For Box unit BPR-WPB
210004403900	Sensor cable 15M	For Box unit BPR-WPB
210004404000	Sensor cable 20M	For Box unit BPR-WPB
210004715600	Sensor cable 25M	For Box unit BPR-WPB
210004404100	Sensor cable 30M	For Box unit BPR-WPB
210004715700	Sensor cable 35M	For Box unit BPR-WPB
210004715800	Sensor cable 40M	For Box unit BPR-WPB
210004715900	Sensor cable 45M	For Box unit BPR-WPB
210004404200	Sensor cable 50M	For Box unit BPR-WPB
210004716000	Sensor cable 55M	For Box unit BPR-WPB
210004716100	Sensor cable 60M	For Box unit BPR-WPB
210004404300	Sensor cable100M	For Box unit BPR-WPB
	Penning gauge	【Option&Parts】
210004463500	Sensor cable 4M	For GI-PA
210004463600	Sensor cable 10M	For GI-PA
210004463700	Sensor cable 15M	For GI-PA
210004463800	Sensor cable 20M	For GI-PA
210004463900	Sensor cable 25M	For GI-PA
210004464000	Sensor cable 30M	For GI-PA
210004487100	Sensor cable 40M	For GI-PA
210004464100	Sensor cable 50M	For GI-PA
210004464200	Sensor cable 4M	For GI-PRYS
210004464400	Sensor cable 10M	For GI-PRYS
200000268000	Sensor cable 20M	For GI-PRYS