

Comparison Chart of Substitution Oil
(Oil “B-50K” for Oil Diffusion Ejector pump PBL series)

Ultimate pressure (Pa)		
Model	ULV01L_B-6	ULV01L_B-50K
PBL-02	2.7×10^{-2}	2.7×10^{-2}
PBL-04		
PBL-06		
PBL-10		
PBL-14		
PBL-20		

Pumping speed (L/s)		
Model	ULV01L_B-6	ULV01L_B-50K
PBL-02	80	80
PBL-04	200	300
PBL-06	500	600
PBL-10	1,800	1,800
PBL-14	4,000	4,000
PBL-20	7,000	8,000

Maximum allowable fore pressure (Pa)		
Model	ULV01L_B-6	ULV01L_B-50K
PBL-02	40	27
PBL-04		40
PBL-06		80
PBL-10		40
PBL-14		90
PBL-20		40